



## WBT-0708 Cu nextgen™ insert Cable lug/solder termination



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 pure white glossy	5666 03	1	77.45	01	4010337461487
 black matt	5666 10	1	77.45	01	4010337461494

### Technische Daten

Connection cross section

- maximum: 1 x 10 mm<sup>2</sup> (7 AWG)
- minimum: 1 x 4 mm<sup>2</sup> (11 AWG)

### Hinweise

- Not suitable for mounting frames with hinged covers.
- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation: Kaiser electronic boxes  
Flush-mounted installation: Kaiser order no.: 1068-02  
Cavity mounting: Kaiser order no.: 9062-94  
Concrete installation: Kaiser order no.: 1268-40