© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

**HDMI insert Gender changer**



| Specification | Order No. | Packing unit | GBP/piece without VAT | PS | EAN |
|---|---|---|---|---|---|
|  pure white glossy | 5669 03 | 1/5 | 116.55 | 01 | 4010337461579 |
|  black matt | 5669 10 | 1/5 | 116.55 | 01 | 4010337461586 |

**Technical data**

| | |
|---|---|
| Installation depth<br>- Gender changer: | mind. 20 mm |

**Notes**

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:Kaiser electronic boxesFlush-mounted installation: Kaiser order no.:1068-02Cavity mounting: Kaiser order no.:9062-94Concrete installation: Kaiser order no.:1268-40

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.