



## Cinch audio and HDMI insert Breakout cable



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 pure white glossy	5674 03	1	168.22	01	4010337461739
 black matt	5674 10	1	168.22	01	4010337461746

### Technische Daten

Installation depth	
- Breakout cable:	mind. 51 mm
Wave impedance for breakout cable:	75 Ω
Length of the breakout cable:	200 mm

### Hinweise

- For screw attachment only.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation: Kaiser electronic boxes  
Flush-mounted installation: Kaiser order no.: 1068-02  
Cavity mounting: Kaiser order no.: 9062-94  
Concrete installation: Kaiser order no.: 1268-40