



HDMI and SAT F jack insert Gender changer



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|---|-------------|-----|--------------------|----|---------------|
|  pure white glossy | 5675 03 | 1/5 | 135.73 | 01 | 4010337461760 |
|  black matt | 5675 10 | 1/5 | 135.73 | 01 | 4010337461777 |

Technische Daten

| | |
|--------------------------|---------------|
| Installation depth | |
| - Gender changer: | mind. 20 mm |
| Wave impedance for SAT: | 75 Ω |
| For internal conductors: | Ø 0.6 to 1 mm |

Hinweise

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation: Kaiser electronic boxes
Flush-mounted installation: Kaiser order no.: 1068-02
Cavity mounting: Kaiser order no.: 9062-94
Concrete installation: Kaiser order no.: 1268-40