



## HDMI and USB 3.0 type A insert Breakout cable



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSSt.	PS	EAN
 pure white glossy	5679 03	1	151.23	01	4010337461890
 black matt	5679 10	1	151.23	01	4010337461883

### Technische Daten

Installation depth	
- Breakout cable:	mind. 51 mm
Length of the breakout cable:	200 mm

### Hinweise

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation: Kaiser electronic boxes  
Flush-mounted installation: Kaiser order no.: 1068-02  
Cavity mounting: Kaiser order no.: 9062-94  
Concrete installation: Kaiser order no.: 1268-40