© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

USB 3.0 type A insert, 2-gang Breakout cable



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 pure white glossy	5685 03	1	60.86	01	4010337462095
 black matt	5685 10	1	60.86	01	4010337462101

Technical data

Installation depth - Breakout cable:	mind. 46 mm
Length of the breakout cable:	200 mm

Notes

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:Kaiser electronic boxesFlush-mounted installation: Kaiser order no.:1068-02Cavity mounting: Kaiser order no.:9062-94Concrete installation: Kaiser order no.:1268-40