© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

USB 3.0 type A and mini jack 3.5 mm insert Gender changer, USB, breakout cable



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 pure white glossy	5686 03	1	55.01	01	4010337462125
 black matt	5686 10	1	55.01	01	4010337462132

Technical data

Installation depth	
- Gender changer:	mind. 20 mm
- Breakout cable:	mind. 46 mm
Length of the breakout cable:	200 mm

Notes

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:Kaiser electronic boxesFlush-mounted installation: Kaiser order no.:1068-02Cavity mounting: Kaiser order no.:9062-94Concrete installation: Kaiser order no.:1268-40