



USB 3.0 type A and mini jack 3.5 mm insert Gender changer, USB, breakout cable, mini jack



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|-----------------------------------------------------------------------------------------------------|-------------|----|--------------------|----|---------------|
|  pure white glossy | 5686 03 | 1 | 55.01 | 01 | 4010337462125 |
|  black matt | 5686 10 | 1 | 55.01 | 01 | 4010337462132 |

Technische Daten

| | |
|-------------------------------|-------------|
| Installation depth | |
| - Gender changer: | mind. 20 mm |
| - Breakout cable: | mind. 46 mm |
| Length of the breakout cable: | 200 mm |

Hinweise

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation: Kaiser electronic boxes
Flush-mounted installation: Kaiser order no.:1068-02
Cavity mounting: Kaiser order no.:9062-94
Concrete installation: Kaiser order no.:1268-40