



USB 3.0 type A and mini jack 3.5 mm insert Gender changer, USB, breakout cable



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 pure white glossy	5686 03	1	55.01	01	4010337462125
 black matt	5686 10	1	55.01	01	4010337462132

Technische Daten

Installation depth	
- Gender changer:	mind. 20 mm
- Breakout cable:	mind. 46 mm
Length of the breakout cable:	200 mm

Hinweise

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation: Kaiser electronic boxes
Flush-mounted installation: Kaiser order no.: 1068-02
Cavity mounting: Kaiser order no.: 9062-94
Concrete installation: Kaiser order no.: 1268-40