



Modular Jack RJ45 cat.6A 10 Gbit Ethernet insert, 4-gang Gender changer



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 pure white glossy	5698 03	1/5	97.98	01	4010337463429
 black matt	5698 10	1/5	97.98	01	4010337463443

Technische Daten

Installation depth
- Gender changer: mind. 24 mm

Hinweise

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation: Kaiser electronic boxes
Flush-mounted installation: Kaiser order no.:1068-02
Cavity mounting: Kaiser order no.:9062-94
Concrete installation: Kaiser order no.:1268-40