

## Rocker for rocker set, 4-gang for pushbutton sensor 4.95



| Specification                                                                                                             | Order No. | Packing unit | GBP/piece<br>without VAT | PS | EAN           |
|---------------------------------------------------------------------------------------------------------------------------|-----------|--------------|--------------------------|----|---------------|
|  aluminium pure white glossy (lacquered) | 8334 903  | 1            | 40.59                    | 06 | 4010337098720 |
|  aluminium pure white matt (lacquered) | 8334 927  | 1            | 40.59                    | 06 | 4010337098744 |
|  aluminium anthracite (lacquered)      | 8334 928  | 1            | 40.59                    | 06 | 4010337098683 |
|  aluminium (anodised)                  | 8334 17   | 1            | 29.77                    | 06 | 4010337096986 |
|  aluminium black matt (lacquered)      | 8334 905  | 1            | 40.59                    | 06 | 4010337098706 |
|  aluminium grey matt (lacquered)       | 8334 915  | 1            | 40.59                    | 06 | 4010337098669 |
|  aluminium black (anodised)            | 8334 126  | 1            | 29.77                    | 06 | 4010337097228 |
|  Bronze (PVD)                          | 8334 38   | 1            | 70.36                    | 06 | 4010337098775 |
|  white glass                           | 8334 12   | 1            | 29.77                    | 06 | 4010337098010 |

|                                                                                   |                 |          |   |       |    |               |
|-----------------------------------------------------------------------------------|-----------------|----------|---|-------|----|---------------|
|  | black glass     | 8334 05  | 1 | 29.77 | 06 | 4010337098034 |
| <hr/>                                                                             |                 |          |   |       |    |               |
|  | stainless steel | 8334 219 | 1 | 54.12 | 06 | 4010337097785 |
| <hr/>                                                                             |                 |          |   |       |    |               |