


## Rocker switch 10 AX 250 V~ with inscription space Universal 1-way/2-way switch



Spezifikation	Bestell-Nr.	VE	PS	EAN
 grey	0106 31	-	-	4010337106319

### Merkmale

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic or would that then be polycarbonate.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Water-protected surface-mounted IP66

### Technische Daten

- Connection cross section
- For rigid and flexible conductors up to: 2.5 mm<sup>2</sup>
- Rated output
- LEDi/CFLi: 100 W

### Hinweise

- Subject to availability.
- Can also be connected to be illuminated.

## Lieferumfang

- Blank inscription label enclosed.

---