







## Gira F300 cover frame black matt (lacquered)



| Spezifikation  | Bestell-Nr. | VE   | PS | EAN           |
|--|-------------|------|----|---------------|
|  1-gang                     | 0211 84     | 1/10 |    | 4010337113508 |
|  2-gang                   | 0212 84     | 1/10 |    | 4010337113553 |
|  2-gang, without crossbar | 1002 84     | 1/10 |    | 4010337131892 |
|  3-gang                   | 0213 84     | 1/5  |    | 4010337113607 |
|  4-gang                   | 0214 84     | 1/5  |    | 4010337113652 |
|  5-gang                   | 0215 84     | 1/5  |    | 4010337131885 |

### Merkmale

- In the Pure White Gloss finish: made from 85% bio-based plastic.

### Technische Daten

|                         |                           |
|-------------------------|---------------------------|
| Cover frame 1-g:        | B 80,8 x H 80,8 x T 11,4  |
| Cover frame 2-g:        | B 80,8 x H 151,9 x T 11,4 |
| Cover frame 2-g w/o cb: | B 80,8 x H 151,9 x T 11,4 |

# GIRA Parts list

catalogue.gira.com

© Copyright by  
Gira Giersiepen GmbH & Co. KG  
All rights reserved

www.gira.com

|  |                           |
|--|---------------------------|
| Cover frame 3-g:   | B 80,8 x H 223,4 x T 11,4 |
| Cover frame 4-g:   | B 80,8 x H 297,7 x T 11,4 |
| Cover frame 5-g:   | B 80,8 x H 366,0 x T 11,4 |
| Corner radius:   | R 0.5                     |
| Biocircular plastic<br>- Colour option: Pure white glossy: | at least 50%              |

---