







## Gira E2 cover frame colour aluminium



Spezifikation	Bestell-Nr.	VE	PS	EAN
 1-gang	0211 25	1/10/100		4010337211259
1-gang	6211 25	1/10/100		4010337105374
 1.5-gang	1001 25	1/10		4010337881346
 2-gang	0212 25	1/10		4010337212256
2-gang	6212 25	1/10		4010337105381
 2-gang, without crossbar	1002 25	1/10		4010337002253
 3-gang	0213 25	1/5		4010337213253
3-gang	6213 25	1/5		4010337105398
 4-gang	0214 25	1/5		4010337214250



5-gang

0215 25

1/5

4010337215257

---

## **Merkmale**

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic or would that then be polycarbonate.

---

## **Hinweise**

- Also suitable for duct installation.
  - In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.
-