

## Electronic potentiometer insert for 1 – 10 V control input Switching function



| Spezifikation   | Bestell-Nr. | VE  | PS | EAN           |
|---|-------------|-----|----|---------------|
|  | 0309 00     | 1/5 |    | 4010337309000 |

### Merkmale

- Electronic potentiometer with switching function for electronic ballasts or Tronic transformers with 1 – 10 V control input.
- Pressing the operating button switches the electronic ballasts on and off.
- Rotating adjusts the brightness.
- Basic brightness can be set.
- Short-circuit protection of the switching contact by integrated fine fuse.

### Technische Daten

|                      |                    |
|----------------------|--------------------|
| Rated voltage:       | AC 230 V, 50/60 Hz |
| 1 – 10 V interface   |                    |
| - Control voltage:   | 0.7 to 12 V        |
| - Control current:   | max. 50 mA         |
| Switching current    |                    |
| - Ohmic:             | 6 A                |
| Installation depth:  | 32 mm              |
| Ambient temperature: | +5 °C to +25 °C    |

### Lieferumfang

- Fuse is included with delivery.