







Gira F300 cover frame grey matt (lacquered)



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|--|-------------|------|----|---------------|
|  1-gang | 0211 86 | 1/10 | | 4010337113492 |
|  2-gang | 0212 86 | 1/10 | | 4010337113522 |
|  2-gang, without crossbar | 1002 86 | 1/10 | | 4010337131915 |
|  3-gang | 0213 86 | 1/5 | | 4010337113577 |
|  4-gang | 0214 86 | 1/5 | | 4010337113621 |
|  5-gang | 0215 86 | 1/5 | | 4010337131908 |

Merkmale

- In the Pure White Gloss finish: made from 85% bio-based plastic.

Technische Daten

| | |
|-------------------------|---------------------------|
| Cover frame 1-g: | B 80,8 x H 80,8 x T 11,4 |
| Cover frame 2-g: | B 80,8 x H 151,9 x T 11,4 |
| Cover frame 2-g w/o cb: | B 80,8 x H 151,9 x T 11,4 |

GIRA Parts list

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

| | |
|--|---------------------------|
| Cover frame 3-g: | B 80,8 x H 223,4 x T 11,4 |
| Cover frame 4-g: | B 80,8 x H 297,7 x T 11,4 |
| Cover frame 5-g: | B 80,8 x H 366,0 x T 11,4 |
| Corner radius: | R 0.5 |
| Biocircular plastic - Colour option: Pure white glossy: | at least 50% |
