




Lighting element for surface-mounted housing



Spezifikation	Bestell-Nr.	VE	PS	EAN
 cream white glossy	1067 01	1/5		4010337105169
 pure white glossy	1067 03	1/5		4010337107088
 black matt	1067 005	1/5		4010337110255

Merkmale

- The white LEDs project a light corridor downwards. This produces indirect orientation light that also avoids bothersome glare in bedrooms.

Technische Daten

Rated voltage:	AC 230 V, 50 Hz
Power consumption:	0.05 W / 1.65 mA
Light intensity:	0.2 cd
Ambient temperature:	0 °C to +40 °C