© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Lighting element for surface-mounted housing



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	1067 01	1/5		4010337105169
 pure white glossy	1067 03	1/5		4010337107088
 black matt (lacquered)	1067 005	1/5		4010337110255

Features

- The white LEDs project a light corridor downwards. This produces indirect orientation light that also avoids bothersome glare in bedrooms.

Technical data

Rated voltage:	AC 230 V, 50 Hz
Power consumption:	0.05 W / 1.65 mA
Light intensity:	0.2 cd
Ambient temperature:	0 °C to +40 °C

Illustrations are similar and may deviate from originals.