










Gira E2 cover frame with inscription space colour aluminium



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|---|-------------|------|----|---------------|
|  1-gang | 1091 25 | 1/10 | | 4010337084051 |
|  2-gang horizontal | 1092 25 | 1/10 | | 4010337084112 |
|  2-gang vertical | 1102 25 | 1/10 | | 4010337084143 |
|  3-gang horizontal | 1093 25 | 1/5 | | 4010337084181 |
|  3-gang vertical | 1103 25 | 1/5 | | 4010337084228 |
|  4-gang horizontal | 1094 25 | 1/5 | | 4010337084266 |
|  4-gang vertical | 1114 25 | 1/5 | | 4010337084303 |
|  5-gang horizontal | 1095 25 | 1/5 | | 4010337084389 |
|  5-gang vertical | 1115 25 | 1/5 | | 4010337084341 |

Merkmale

- Shatter-proof.
 - Spray-proof.
 - Frames with transparent view window for inscription.
 - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
 - Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
-

Hinweise

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-