

Light bulb dimming insert with pressure/2-way switch



Spezifikation	Bestell-Nr.	VE	PS	EAN
 100–1000 W	1181 00	1/5		4010337003939

Merkmale

- Dimming light bulbs and HV halogen lamps at AC 230 V, 50 Hz.
- Electronic short-circuit protection.
- Automatic excess-temperature protection with restart.
- With screw terminals.

Technische Daten

Rated voltage:	AC 230/240 V, 50 Hz
Connected load at 25 °C	
- Light bulbs:	100 to 1000 W
- HV halogen lamps:	100 to 1000 W
Installation depth:	32 mm
Ambient temperature:	+5 °C to +45 °C

Hinweise

- If the ambient temperature is higher than 25 °C, the connected load must be reduced.