


Add-on module for built-in speaker



Spezifikation	Bestell-Nr.	VE	PS	EAN
	1259 00	1		4010337259008

Merkmale

- Installation in a conventional flush-mounted device box.
- Fits in the cover frames of the Gira TX_44 switch range.
- Modular design, allowing easy installation and expandability.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- Up to twelve mechanical bell buttons can be connected.
- Additional bell buttons can be connected via additional add-on modules.
- Up to eleven add-on modules can be connected to one built-in speaker.
- Alternating current polling of the bell button connections to prevent oxidation on the button contacts.
- Compact size.
- Securing of connection terminals against incorrect connection.
- Attachment of the add-on module with screws or gluing.

Technische Daten

Connecting the connection cable:	2 x connector strip
Protection class:	IP44
Power supply:	via connection cable
Connections	
- Mech. Bell button:	12 x screw terminal
- Common earth of bell buttons:	1 x screw terminal
- Connection cable:	2 x connector strip
Ambient temperature:	-25 °C to +70 °C
Dimensions	
- incl. fixing lug:	W 67 x H 66.4 x D 27 mm
- without fixing lug:	W 67 x H 56 x D 27 mm

Hinweise

- Module for extension of the built-in speaker when more than eight mechanical bell buttons are to be connected.
 - This component enables door communication systems with up to 140 audio devices to be set up (e.g. 1 x built-in speaker, 11 x add-on modules for built-in speakers, 136 x surface-mounted home stations).
 - Protection type IP44 only in combination with a suitable front or when installed.
-

Lieferumfang

- The mounting materials are included with delivery.
-