



Light profile height 769 mm



Spezifikation	Bestell-Nr.	VE	PS	EAN
 anthracite	1343 28	1		4010337343288
 colour aluminium	1343 26	1		4010337343264

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

Merkmale

- The light element consists of an aluminium reflector and an impact-resistant acrylic glass plate.
- Light is also emitted from the rear as orientation lighting.
- A 5-pole screw terminal for rigid and flexible conductors up to 4 mm² is used for connection.

Technische Daten

Protection class:	IP44
Dimensions	
- Base:	W 229 x H 10 x D 155 mm
- Profile:	W 142 x H 769 x D 75 mm

Hinweise

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
 - For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
 - Recommendation: Mount an RCCB prior to the device.
 - Single wall plug mounting.
 - Suitable for E27 light sources with energy efficiency classes A++ to E.
-

Lieferumfang

- The mounting materials are included with delivery.
 - Light sources are not included with delivery.
-