



## Gira energy profile with 6 empty units height 769 mm not equipped



Spezifikation	Bestell-Nr.	VE	PS	EAN
 anthracite	1351 28	1		4010337351283
 colour aluminium	1351 26	1		4010337351269

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

### Merkmale

- Freely configurable Gira energy profile with 6 empty units.
- The six empty units can be individually equipped with device inserts from the Gira TX\_44 design line or from System 55 by the customer.

### Technische Daten

Protection type (device cover closed):	IP44
Dimensions	
- Base:	W 229 x H 10 x D 155 mm
- Profile:	W 142 x H 769 x D 75 mm

### Hinweise

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
  - For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
  - Recommendation: Mount an RCCB prior to the device.
  - Single wall plug mounting.
- 

## **Lieferumfang**

- Two cover frames Gira TX\_44, 3-gang are included with delivery.
  - The mounting materials are included with delivery.
-