



Gira energy profile with light element and 3 empty units height 1600 mm not equipped



Spezifikation	Bestell-Nr.	VE	PS	EAN
 anthracite	1353 28	1		4010337353287
 colour aluminium	1353 26	1		4010337353263

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

Merkmale

- Freely configurable Gira energy profile with 3 empty units and light element.
- The light element consists of an aluminium reflector and an impact-resistant acrylic glass plate.
- Light is also emitted from the rear as orientation lighting.
- The three empty units can be individually equipped with device inserts from the TX_44 design line or from System 55 by the customer.

Technische Daten

Protection type (device cover closed):	IP44
Dimensions	
- Base:	W 229 x H 10 x D 155 mm
- Profile:	W 142 x H 1600 x D 75 mm

Hinweise

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
 - For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
 - Recommendation: Mount an RCCB prior to the device.
 - Mounting using three heavy-duty wall anchors.
 - Suitable for E27 light sources with energy efficiency classes A++ to E.
 - Any required electrical isolation of mains and low voltage can be implemented with the included accessories.
-

Lieferumfang

- Cover frame, 3-gang TX_44 is included with delivery.
 - The mounting materials are included with delivery.
 - Light sources are not included with delivery.
-