


IP interface for KNX



Spezifikation	Bestell-Nr.	VE	PS	EAN
 DRA	2168 00	1		4010337084457

Merkmale

- For coupling a PC to the KNX bus to address, program, or diagnose KNX components.

Technische Daten

KNX medium:	KNXnet/IP and TP1-256
Rated voltage:	DC 24 to 30 V
IP communication:	Ethernet 10/100 BaseT (10/100 Mbit/s)
Supported protocols:	ARP, ICMP, IGMP, DHCP, AutoIP, UDP/IP (Core, Tunnelling, Device Management)
Connections	
- IP:	2 x RJ45 jacks
- KNX:	Connection and junction terminal
Ambient temperature:	0 °C to +45 °C

Hinweise

- Power supply via external DC 24 V or via unchoked output of the Gira power supply for KNX.

Abmessungen

Teilungseinheiten (TE):	2
-------------------------	---