









## Speaker flush-mounted radio IP



| Spezifikation   | Bestell-Nr. | VE | PS | EAN           |
|---|-------------|----|----|---------------|
|  cream white glossy  | 2282 01     | 1  |    | 4010337076230 |
|  pure white glossy | 2282 03     | 1  |    | 4010337076247 |
|  pure white matt   | 2282 27     | 1  |    | 4010337076254 |
|  anthracite        | 2282 28     | 1  |    | 4010337076261 |
|  colour aluminium  | 2282 26     | 1  |    | 4010337076162 |
|  black matt        | 2282 005    | 1  |    | 4010337037286 |
|  grey matt         | 2282 015    | 1  |    | 4010337083931 |
|  stainless steel   | 2282 600    | 1  |    | 4010337032861 |

## Merkmale

- Speaker for connection to the Gira flush-mounted radio.

---

## Technische Daten

|   |                     |
|---|---------------------|
| Installation depth:                                   | 32 mm               |
| Connection cross section<br>- Speaker/AUX connection: | 1.5 mm <sup>2</sup> |
| Impedance:  | 8 Ω                 |
| Ambient temperature:                                  | -5 °C to +50 °C     |

---