






EnOcean wireless wall transmitter, 1-gang System 55



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|---|-------------|----|----|---------------|
|  cream white glossy | 2421 01 | 1 | | 4010337463825 |
|  pure white glossy | 2421 03 | 1 | | 4010337463832 |
|  pure white matt | 2421 27 | 1 | | 4010337463849 |
|  anthracite | 2421 28 | 1 | | 4010337463856 |
|  colour aluminium | 2421 26 | 1 | | 4010337463870 |
|  black matt | 2421 005 | 1 | | 4010337037088 |
|  grey matt | 2421 015 | 1 | | 4010337084136 |

Merkmale

- Wireless transmitter for transmitting switching, dimming and blind commands to wireless receivers in the EnOcean wireless system.
- Battery-free device without external power supply. The transmission energy is generated from mechanical energy by actuating the rocker.
- Encrypted or unencrypted wireless transmission possible.

Technische Daten

| | |
|----------------------|----------------------------------|
| Wireless frequency: | 868.3 MHz |
| Range | |
| - in free field: | up to 300 m |
| - in buildings: | approx. 30 m |
| Ambient temperature: | -25 °C to +65 °C |
| Humidity: | 0 to 95 % (without condensation) |

Hinweise

- Mounting on device box or on smooth, level surfaces using screws or adhesives.
 - This product cannot be used with eNet. Gira EnOcean transmitters are compatible with third-party actuators.
-

Lieferumfang

- Radio wall transmitter, comes with mounting plate, adhesive film (privacy protection for glass surfaces), and adhesive points for installation on smooth, level surfaces.
-