GIRA Data sheet

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

EnOcean wireless wall transmitter, 2-gang System 55



Specification	Order No.	Packing unit	PS	EAN
cream white glossy	2422 01	1		4010337060420
pure white glossy	2422 03	1		4010337060437
pure white matt	2422 27	1		4010337060451
anthracite	2422 28	1		4010337060468
colour aluminium (lacquered)	2422 26	1		4010337060444
black matt (lacquered)	2422 005	1		4010337037095
grey matt (lacquered)	2422 015	1		4010337084648

Features

- Wireless transmitter for transmitting switching, dimming and blind commands to wireless receivers in the EnOcean wireless system.
- Battery-free device without external power supply. The transmission energy is generated from mechanical energy by actuating the rocker.
- Encrypted or unencrypted wireless transmission possible.

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Technical data

Wireless frequency:	868.3 MHz
Range	
- in free field:	up to 300 m
- in buildings:	approx. 30 m
Ambient temperature:	-25 °C to +65 °C
Humidity:	0 to 95 % (without condensation)

Notes

- Mounting on device box or on smooth, level surfaces using screws or adhesives.
- This product cannot be used with eNet. Gira EnOcean transmitters are compatible with third-party actuators.

Scope of supply

- Radio wall transmitter, comes with mounting plate, adhesive film (privacy protection for glass surfaces), and adhesive points for installation on smooth, level surfaces.
