







EnOcean wireless wall transmitter, 2-gang System 55



Spezifikation	Bestell-Nr.	VE	PS	EAN
 cream white glossy	2422 01	1		4010337060420
 pure white glossy	2422 03	1		4010337060437
 pure white matt	2422 27	1		4010337060451
 anthracite	2422 28	1		4010337060468
 colour aluminium	2422 26	1		4010337060444
 black matt	2422 005	1		4010337037095
 grey matt	2422 015	1		4010337084648

Merkmale

- Wireless transmitter for transmitting switching, dimming and blind commands to wireless receivers in the EnOcean wireless system.
- Battery-free device without external power supply. The transmission energy is generated from mechanical energy by actuating the rocker.
- Encrypted or unencrypted wireless transmission possible.

Technische Daten

Wireless frequency:	868.3 MHz
Range	
- in free field:	up to 300 m
- in buildings:	approx. 30 m
Ambient temperature:	-25 °C to +65 °C
Humidity:	0 to 95 % (without condensation)

Hinweise

- Mounting on device box or on smooth, level surfaces using screws or adhesives.
 - This product cannot be used with eNet. Gira EnOcean transmitters are compatible with third-party actuators.
-

Lieferumfang

- Radio wall transmitter, comes with mounting plate, adhesive film (privacy protection for glass surfaces), and adhesive points for installation on smooth, level surfaces.
-