


System 3000 LED rotary dimming insert Basic RC



Spezifikation	Bestell-Nr.	VE	PS	EAN
	2457 00	1/5		4010337131458

Merkmale

- Device operates on trailing edge principle.
- It is switched on with a bulb-saving soft start.
- Push-button/2-way switch for integration in 2-way switching and intermediate switching configurations.
- Minimum brightness can be adjusted.
- Maximum brightness can be adjusted.
- Electronic short-circuit and overload protection.
- Electronic excess-temperature protection.
- No neutral conductor required.

Technische Daten

Rated voltage:	AC 230 V, 50/60 Hz
Standby:	None
Connected load at 35°C:	
- HV LED lamps (trailing edge):	Typically 3 to 200 W
- Light bulbs:	3 to 200 W
- HV halogen lamps:	3 to 200 W
- Electronic transformer with LV LED (trailing edge):	Typically 3 to 200 W
Cable length	
- Load:	Max. 100 m
Installation depth:	24 mm
Installation:	in device box in accordance with DIN 49073
Ambient temperature:	0°C to +35°C