GIRA Data sheet

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

SCHUKO socket outlet, 16 A 250 V~ with increased contact protection (Safety Plus) and USB power supply, 2-gang Type A / type C



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	2459 01	1		4010337076223
 pure white glossy	2459 03	1		4010337076179
 pure white matt	2459 27	1		4010337076186
 anthracite	2459 28	1		4010337076285
 colour aluminium (lacquered)	2459 26	1		4010337076193
 black matt (lacquered)	2459 005	1		4010337076209
 grey matt (lacquered)	2459 015	1		4010337090151
 stainless steel (lacquered)	2459 600	1		4010337076148

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Features

- Charging option for up to two end devices simultaneously using USB cable type A and type C.
- Up to two end devices can be charged simultaneously.

Technical data

Input voltage:	AC 220 – 250 V, 50/60 Hz
USB connection:	1 x type A, 1 x type C
Output voltage USB:	DC 5 V
Charging current	
- USB A:	max. 2.4 A
- USB C:	Max. 3 A
Standby:	≤80 mW
Connection cross section	
- for conductors from:	1.5 mm² to 2.5 mm²
Installation depth:	31 mm
Ambient temperature:	+5° C to +35° C

Notes

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
- During long charging cycles, the housing of the product may heat up.
- Using a deep device box is recommended.

Scope of supply

- Type A or type C USB cables are not included with delivery.
