

SCHUKO socket outlet, 16 A 250 V~ with increased contact protection (Safety Plus) and USB power supply, 2-gang Type A / type C



Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	2459 70	1		4010337129967
 pure white matt (lacquered)	2459 72	1		4010337137689
 anthracite (lacquered)	2459 73	1		4010337137696
 black matt (lacquered)	2459 74	1		4010337137702
 grey matt (lacquered)	2459 76	1		4010337137719

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.
- Charging option for up to two end devices simultaneously using USB cable type A and type C.
- Up to two end devices can be charged simultaneously.

Technical data

Input voltage:	AC 220 – 250 V, 50/60 Hz
USB connection:	1 x type A, 1 x type C
Output voltage USB:	DC 5 V
Charging current	
- USB A:	max. 2.4 A
- USB C:	Max. 3 A
Standby:	≤80 mW
Connection cross section	
- for conductors from:	1.5 mm ² to 2.5 mm ²
Installation depth:	31 mm
Ambient temperature:	+5° C to +35° C

Notes

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
- During long charging cycles, the housing of the product may heat up.
- Using a deep device box is recommended.

Scope of supply

- Type A or type C USB cables are not included with delivery.
-