© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

**Bluetooth® wall transmitter, 2-gang**



| Specification | Order No. | Packing unit | PS | EAN |
|---|---|---|---|---|
| cream white glossy | 2462 01 | 1 | | 4010337110736 |
| pure white glossy | 2462 03 | 1 | | 4010337101642 |
| pure white matt | 2462 27 | 1 | | 4010337101659 |
| anthracite | 2462 28 | 1 | | 4010337101680 |
| colour aluminium (lacquered) | 2462 26 | 1 | | 4010337101673 |
| black matt (lacquered) | 2462 005 | 1 | | 4010337101666 |
| grey matt (lacquered) | 2462 015 | 1 | | 4010337110743 |

**Features**

- Wireless transmitter for transmitting switching, dimming or blind commands to the Bluetooth® wireless receivers from the System 3000 or third parties, e.g Casambi.
- Battery-free device without external power supply. The transmission energy is generated from mechanical energy by actuating the rocker.
- Configuration via the app or NFC.

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Technical data**

| | |
|---|---|
| Wireless frequency: | 2.402 - 2.480 GHz |
| Wireless protocol: | Bluetooth® low energy (BLE) |
| Interface: | NFC |
| Range | |
| - in free field: | up to 75 m |
| - in buildings: | approx. 10 m |
| Ambient temperature: | -25 °C to +65 °C |
| Humidity: | 0 to 95 % (without condensation) |

---

**Notes**

- Mounting on device box or on smooth, level surfaces using screws or adhesives.
- This product cannot be used with eNet.

---

**Scope of supply**

- Radio wall transmitter, comes with mounting plate, adhesive film (privacy protection for glass surfaces), and adhesive points for installation on smooth, level surfaces.

---