

## Bluetooth® wall transmitter, 2-gang



| Spezifikation   | Bestell-Nr. | VE | PS | EAN           |
|---|-------------|----|----|---------------|
|  cream white glossy  | 2462 01     | 1  |    | 4010337110736 |
|  pure white glossy | 2462 03     | 1  |    | 4010337101642 |
|  pure white matt   | 2462 27     | 1  |    | 4010337101659 |
|  anthracite        | 2462 28     | 1  |    | 4010337101680 |
|  colour aluminium  | 2462 26     | 1  |    | 4010337101673 |
|  black matt        | 2462 005    | 1  |    | 4010337101666 |
|  grey matt         | 2462 015    | 1  |    | 4010337110743 |

### Merkmale

- Wireless transmitter for transmitting switching, dimming or blind commands to the Bluetooth® wireless receivers from the System 3000 or third parties, e.g Casambi.
- Battery-free device without external power supply. The transmission energy is generated from mechanical energy by actuating the rocker.
- Configuration via the app or NFC.

## Technische Daten

|                      |                                  |
|----------------------|----------------------------------|
| Wireless frequency:  | 2.402 - 2.480 GHz                |
| Wireless protocol:   | Bluetooth® low energy (BLE)      |
| Interface:           | NFC                              |
| Range                |                                  |
| - in free field:     | up to 75 m                       |
| - in buildings:      | approx. 10 m                     |
| Ambient temperature: | -25 °C to +65 °C                 |
| Humidity:            | 0 to 95 % (without condensation) |

---

## Hinweise

- Mounting on device box or on smooth, level surfaces using screws or adhesives.
  - This product cannot be used with eNet.
- 

## Lieferumfang

- Radio wall transmitter, comes with mounting plate, adhesive film (privacy protection for glass surfaces), and adhesive points for installation on smooth, level surfaces.
-