








British Standard fused spur connection unit (BS 1363-4) 13 A 250 V~ switched, with control light System 55



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|---|-------------|-----|----|---------------|
|  cream white glossy | 2787 01 | 1/5 | | 4010337080053 |
|  pure white glossy | 2787 03 | 1/5 | | 4010337080060 |
|  anthracite | 2787 28 | 1/5 | | 4010337080084 |
|  colour aluminium | 2787 26 | 1/5 | | 4010337080077 |
|  black matt | 2787 005 | 1/5 | | 4010337037118 |
|  grey matt | 2787 015 | 1/5 | | 4010337087052 |
|  stainless steel (lacquered) | 2787 600 | 1/5 | | 4010337022190 |

Merkmale

- With screw terminals.
- For screw attachment only.

Technische Daten

Installation depth: 29 mm
