







British Standard Fused spur connection box (BS 1363-4) 13 A 250 V~ not switched System 55



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|---|-------------|-----|----|---------------|
|  cream white glossy | 2811 01 | 1/5 | | 4010337035824 |
|  pure white glossy | 2811 03 | 1/5 | | 4010337035831 |
|  anthracite | 2811 28 | 1/5 | | 4010337035848 |
|  colour aluminium | 2811 26 | 1/5 | | 4010337035855 |
|  black matt | 2811 005 | 1/5 | | 4010337053354 |
|  grey matt | 2811 015 | 1/5 | | 4010337087083 |
|  stainless steel (lacquered) | 2811 600 | 1/5 | | 4010337035879 |

Merkmale

- With screw terminals.
- For screw attachment only.

Technische Daten

Installation depth: 29 mm

Connection cross section
- maximum: 2 x 2.5 mm²
