








British Standard rocker switch (BS EN 60669-1) 3-gang with rockers 1-way switch



Spezifikation	Bestell-Nr.	VE	PS	EAN
 cream white glossy	2830 01	1/10		4010337830016
 pure white glossy	2830 03	1/10		4010337830030
 anthracite	2830 28	1/10		4010337830283
 colour aluminium	2830 26	1/10		4010337830269
 black matt	2830 005	1/10		4010337038580
 grey matt	2830 015	1/10		4010337087113
 stainless steel (lacquered)	2830 600	1/10		4010337022022

Technische Daten

Installation depth:	25 mm
Connection cross section - for conductors up to:	2.5 mm ²
Rated output:	100 W LED load (IEC 60669)