








Rocker switch, 3-gang, 10 AX 250 V~ with rockers Universal 1-way/2-way switch



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|---|-------------|------|----|---------------|
|  cream white glossy | 2832 01 | 1/10 | | 4010337832010 |
|  pure white glossy | 2832 03 | 1/10 | | 4010337832034 |
|  anthracite | 2832 28 | 1/10 | | 4010337832287 |
|  colour aluminium | 2832 26 | 1/10 | | 4010337832263 |
|  black matt | 2832 005 | 1/10 | | 4010337038528 |
|  grey matt | 2832 015 | 1/10 | | 4010337087120 |
|  stainless steel (lacquered) | 2832 600 | 1/10 | | 4010337022053 |

Technische Daten

| | |
|---|---------------------|
| Installation depth: | 25 mm |
| Connection cross section - for conductors up to: | 2.5 mm ² |

Hinweise

- For screw attachment only.
