

## Socket outlet with protective contact EURO-US 16 A 250 V~



| Spezifikation                                                                                                   | Bestell-Nr. | VE   | PS | EAN           |
|-----------------------------------------------------------------------------------------------------------------|-------------|------|----|---------------|
|  cream white glossy            | 2840 01     | 1/10 |    | 4010337840015 |
|  pure white glossy           | 2840 03     | 1/10 |    | 4010337840039 |
|  pure white matt             | 2840 27     | 1/10 |    | 4010337840275 |
|  anthracite                  | 2840 28     | 1/10 |    | 4010337840282 |
|  colour aluminium            | 2840 26     | 1/10 |    | 4010337840268 |
| black matt                                                                                                      | 2840 005    | 1/10 |    | 4010337037873 |
|  grey matt                   | 2840 015    | 1    |    | 4010337087151 |
|  stainless steel (lacquered) | 2840 600    | 1/10 |    | 4010337022213 |

### Technische Daten

Installation depth: 20 mm