

## Rocker button, 3-gang 10 A 250 V~ with rockers NO contact, 1-pole



| Specification                                                                                                    | Order No. | Packing unit | PS | EAN           |
|------------------------------------------------------------------------------------------------------------------|-----------|--------------|----|---------------|
|  cream white glossy             | 2844 01   | 1/10         |    | 4010337082033 |
|  pure white glossy            | 2844 03   | 1/10         |    | 4010337082040 |
|  anthracite                   | 2844 28   | 1/10         |    | 4010337082064 |
|  colour aluminium (lacquered) | 2844 26   | 1/10         |    | 4010337082057 |
|  black matt (lacquered)       | 2844 005  | 1/10         |    | 4010337037903 |
|  grey matt (lacquered)        | 2844 015  | 1/10         |    | 4010337087182 |
|  stainless steel (lacquered)  | 2844 600  | 1/10         |    | 4010337021957 |

### Technical data

Installation depth: 25 mm

Connection cross section  
- for conductors up to: 2.5 mm<sup>2</sup>

## Notes

- For screw attachment only.

---