








Rocker button, 3-gang 10 A 250 V~ with rockers NO contact, 1-pole



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|---|-------------|------|----|---------------|
|  cream white glossy | 2844 01 | 1/10 | | 4010337082033 |
|  pure white glossy | 2844 03 | 1/10 | | 4010337082040 |
|  anthracite | 2844 28 | 1/10 | | 4010337082064 |
|  colour aluminium | 2844 26 | 1/10 | | 4010337082057 |
|  black matt | 2844 005 | 1/10 | | 4010337037903 |
|  grey matt | 2844 015 | 1/10 | | 4010337087182 |
|  stainless steel (lacquered) | 2844 600 | 1/10 | | 4010337021957 |

Technische Daten

| | |
|---|---------------------|
| Installation depth: | 25 mm |
| Connection cross section - for conductors up to: | 2.5 mm ² |

Hinweise

- For screw attachment only.
