

## Rocker switch 10 AX 250 V~ Universal 1-way/2-way switch



| Spezifikation  | Bestell-Nr. | VE       | PS | EAN           |
|--|-------------|----------|----|---------------|
|  grey | 3106 30     | 1/10/100 | 24 | 4010337123927 |

### Merkmale

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Water-protected surface-mounted IP44

### Technische Daten

Connection cross section  
- For rigid and flexible conductors up to: 2.5 mm<sup>2</sup>

Rated output  
- LEDi/CFLi: 100 W

### Hinweise

- Can also be connected to be illuminated.