© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Rocker switch insert 10 AX 250 V~ intermediate switch



Specification	Order No.	Packing unit	PS	EAN
 with mounting claws	3107 00	1/10/100		4010337039174
 without mounting claws	3817 00	1/10		4010337039181

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- LED lighting elements can be inserted from the front as standard.

Technical data

Installation depth
- 3107 00: 32 mm
- 3817 00: 23 mm

Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²

Rated output
- LEDi/CFLi: 100 W

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Notes

- Can also be connected to be illuminated.

Illustrations are similar and may deviate from originals.