


Rocker switch insert 10 AX 250 V~ intermediate switch



Specification	Order No.	Packing unit	PS	EAN
 with mounting claws	3107 00	1/10/100		4010337039174
 without mounting claws	3817 00	1/10		4010337039181

Features

- Quick mounting (3.5 turns per mounting claw).
- Voltage check possible from the front.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.

Technical data

Installation depth	
- 3107 00:	32 mm
- 3817 00:	23 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm²
Rated output	
- LEDi/CFLi:	100 W

Notes

- Can also be connected to be illuminated.
