




Rocker indicator switch insert 10 AX 250 V~ with orange LED lighting element element 230 V~ circuit breaker, 2-pole



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|--|-------------|------|----|---------------|
|  with mounting claws | 3112 00 | 1/10 | | 4010337038696 |
|  without mounting claws | 3822 00 | 1 | | 4010337038702 |

Merkmale

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.

Technische Daten

| | |
|--|---------------------|
| Installation depth | |
| - 3112 00: | 32 mm |
| - 3822 00: | 23 mm |
| Connection cross section | |
| - For rigid and flexible conductors up to: | 2.5 mm ² |
| Rated output | |
| - LEDi/CFLi: | 100 W |

Hinweise

- Can also be connected to be illuminated by rotating the LED insert by 180°.

Lieferumfang

- Orange LED lighting element 230 V~ 0.5 mA is included with delivery.
