© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Rocker indicator switch 10 AX 250 V~ with inscription space and orange LED lighting element 230 V~ Circuit breaker, 2-pole



Specification	Order No.	Packing unit	PS	EAN
 grey	3112 30	1/10		4010337123873

Features

- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- With orange LED lighting element.
- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic” or would that then be polycarbonate.

Technical data

Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²

Rated output
- LEDi/CFLi: 100 W

Notes

- Can also be connected to be illuminated.

Scope of supply

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

- Inscription label "Heizung Ein/Aus" is enclosed.
- Cable entry 2-gang (twin entry) is enclosed.
- Orange LED lighting element 230 V~ 0.5 mA is included with delivery.

Illustrations are similar and may deviate from originals.