© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Rocker indicator switch 10 AX 250 V~ with mounting plate and orange LED lighting element 230 V~ Universal 1-way/2-way switch



Specification	Order No.	Packing unit	PS	EAN
 pure white	3116 13	1/10		4010337112471

Features

- With LED lighting element.
- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic” or would that then be polycarbonate.

Technical data

Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²

Rated output
- LEDi/CFLi: 100 W

Notes

- Can also be connected to be illuminated.

Scope of supply

- All devices are delivered including mounting plate, cable and duct entries.
- Orange LED lighting element 230 V~ 0.5 mA is included with delivery.

Illustrations are similar and may deviate from originals.