© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Insert pushbutton switch 10 AX 250 V~ universal off/2-way switch



Specification	Order No.	Packing unit	PS	EAN
 with mounting claws	3126 00	1/10/100		4010337039020
 without mounting claws	3836 00	1/10		4010337038962

Features

- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- The resulting uniform rocker position gives the electrical installation an organised, premium appearance.
- The aesthetics are greatly enhanced, especially with multiple combinations, for example housing several switches in one frame.

Technical data

Installation depth	
- 3126 00:	32 mm
- 3836 00:	23 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm²
Rated output	
- LEDi/CFLi:	100 W

Notes

- Can also be connected to be illuminated.

Illustrations are similar and may deviate from originals.