
© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Insert pushbutton switch 10 AX 250 V~2-way switch, 2-gang



Specification	Order No.	Packing unit	PS	EAN
 with mounting claws	3128 00	1/10		4010337039075
 without mounting claws	3838 00	1		4010337064411

Features

- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- The resulting uniform rocker position gives the electrical installation an organised, premium appearance.
- The aesthetics are greatly enhanced, especially with multiple combinations, for example housing several switches in one frame.

Technical data

Installation depth:	32 mm
Connection cross section - For rigid and flexible conductors up to:	 2.5 mm²
Rated output - LEDi/CFLi:	 100 W

Illustrations are similar and may deviate from originals.