© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Pushbutton indicator switch insert 10 AX 250 V~ with orange LED lighting element 230 V~ series switch



Specification	Order No.	Packing unit	PS	EAN
 with mounting claws	3135 00	1/10		4010337038917
 without mounting claws	3845 00	1/10		4010337064398

Features

- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- The resulting uniform rocker position gives the electrical installation an organised, premium appearance.
- The aesthetics are greatly enhanced, especially with multiple combinations, for example housing several switches in one frame.

Technical data

Installation depth
- 3135 00: 32 mm
- 3845 00: 23 mm

Rated output
- LEDi/CFLi: 100 W

Scope of supply

- Orange LED lighting element 230 V~ 0.5 mA is included with delivery.

Illustrations are similar and may deviate from originals.